

VIAVI

Tunable DBR Laser (mTLG-C2)

MAP Series Distributed Bragg Reflector Laser

The Multiple Application Platform (MAP series) Tunable Distributed Bragg Reflector (DBR) Laser (mTLG-C2) is a next-generation tunable laser that is ideal for DWDM testing that requires changing the wavelength on demand over the C- and L-band with 50 GHz spacing.



The mTLG-C2 is based on a Sampled Grating Distributed Bragg Reflector (SG-DBR) laser with an integral wavelength locker. Wavelength and output power settings can be controlled using the MAP series local interface or automation interfaces. The integrated wavelocker and automatic power control loop provide stable operation. The mTLG-C2 module is a new generation tunable laser module, which is ideal for DWDM testing where the capability to change.

Functional Description

The mTLG laser modules integrate up to 4 VIAVI Transmit Optical Sub-Assembly TOSA-based Integrable Tunable Laser Assemblies (ITLA) that incorporate an SG-BGR, a Semiconductor Optical Amplifier (SOA), and an integral wavelength locker, all enclosed in a high reliability, hermetically sealed (TOSA) package.

Key Features and Benefits


- Single, dual, or quad channel configurations are available
- C- or L-band tunability
- 42 nm C-band wavelength tuning range (36 nm L-band)
- 50 GHz channel spacing
- Narrow linewidth <5 MHz
- >12 dBm C-band output power (>10.5 dBm L-band)
- SMSR 40 dB min

Applications

- Optical amplifier testing
- Tunable laser grids
- DWDM transmission testing
- Fiber characterization
- Transmitter and receiver testing

Compliance

- The MAP Tunable DBR Laser, when installed in a MAP chassis, complies with CE, CSA/UL/ IEC61010-1, plus LXI class C requirements and meets the standard IEC 60825-1 class 1M requirements



An intuitive graphic user interface (GUI) is optimized for use in either a laboratory or a manufacturing environment. Efficient transition between summary and detailed views (Figure 1 and Figure 2) allow users to operate at a system level or access the full power of a module.

2 TLG 8202		
Power	Frequency	
13.000 dBm	193.400 THz	
Power	Frequency	
13.000 dBm	193.400 THz	
Power	Frequency	
13.000 dBm	193.400 THz	
Power	Frequency	
13.000 dBm	193.400 THz	

Figure 1 – mTLG MAP-300 summary view GUI

← 2 TLG 8202 |

DEVICE 1 DEVICE 2 DEVICE 3 DEVICE 4 ⚙️

Laser State

Source

Power: 13.000 dBm Power Offset: 0.00 dBm

Band Type: C-Band

Laser Frequency

Units:

Value: 193.400 THz

Figure 2 – mTLG MAP-300 detailed view GUI

Options and Configurations

The TLG laser module advances the optical source capability by offering C or L band tunability, and dense configurations with 1, 2 or 4 sources per module.

Chassis and Modular Family

The VIAVI Multiple Application Platform (MAP) is a modular, rack mountable or benchtop, optical test and measurement platform with chassis' that can host 2, 3 or 8 application modules. The LightDirect family of modules are characterized by their simple control and single function nature. Individually or together they form the foundation of a diverse array of optical test applications. The web enabled multiuser interface is simple and intuitive. LXI compliant with a full suite of SCPI based automation drivers and PC based management tools, the VIAVI MAP is optimized for both the lab to manufacturing environments.

The mTLG is part of the LightDirect module family. Alongside the many other modules, such as light sources, polarization scramblers, power meters, and spectrum analyzers, the MAP series is the ideal, modular platform for photonic system and module testing.

The mTLG is compatible with all current MAP-300 and MAP-200 chassis.



Light Direct

Specifications

For more information on this or other products and their availability, please contact your local VIAVI account manager or VIAVI directly at 1-844-GO-VIAVI (1-844-468-4284) or to reach the VIAVI office nearest you, visit viavisolutions.com/contacts.

Parameters	C-band	L-band
Wavelength		
Tuning range	191.0 to 196.25 THz, 1527.60 to 1569.59 nm	186.35 to 190.90 THz, 1570.42 to 1608.76 nm
Accuracy ^{1,2,3}	±2 GHz (±0.016 nm)	
Stability 15 minutes ^{1,2,3}	±0.005 nm typical	
Stability 24 hours ^{1,2,3}	±0.01 nm typical	
Channel spacing	50 GHz (0.431 nm)	
Power		
Setting range ⁴	7.5 to 13 dBm	7 to 10.5 dBm
Stability 15 minutes ^{1,2,3}	±0.005 dB typical	
Stability 24 hours ^{1,2,3}	±0.03 dB typical	
Resolution	<0.1 dB typical	
Spectral properties		
Linewidth ⁵	≤5 MHz	
RIN	-140 dB/Hz typical; -135 dB/Hz max	
SMSR	40 dB min	
Other		
Fiber type	Polarization maintaining fiber; polarization aligned to slow axis and connector	
Warm-up time ²	1 hour	
Supported connectors	FC/APC	
Humidity	<80% RH, 10 to 40°C noncondensing	
Operating temperature	10 to 40°C	
Dimensions	4.06 x 13.26 x 37.03 (1.6 x 5.22 x 14.58 in)	
Weight	1.3 kg (2.95 lb) maximum (varies with configuration)	
Warranty	3 Years	
Calibration period	1 Year	

1. At full power

2. After 1-hour warm up

3. Constant temperature within 25 ±3°C

4. Power at max setting: >12 dBm for C-band and >10.5 dBm for L-band

5. Natural (instantaneous) linewidth of the laser; with self-homodyne measurements indicated linewidth is typically

Ordering Information

Part Number	Description
MTLG-C2C10-M100-MFA	Single C-band 50GHz step tunable laser, single mode FC/APC
MTLG-C2C20-M100-MFA	Dual C-band 50GHz step tunable laser, single mode FC/APC
MTLG-C2C40-M100-MFA	Quad C-band 50GHz step tunable laser, single mode FC/APC
MTLG-C2L10-M100-MFA	Single L-band 50GHz step tunable laser, single mode FC/APC
MTLG-C2L20-M100-MFA	Dual L-band 50GHz step tunable laser, single mode FC/APC
MTLG-C2L40-M100-MFA	Quad L-band 50GHz step tunable laser, single mode FC/APC
MTLG-C2C1L1-M100-MFA	Single C-band and L-band 50GHz step tunable laser, single mode FC/APC

Accessories

Accessories (Optional)	Product and description	
Inspection and cleaning tool	CleanBlast	The patented VIAVI Solutions® CleanBlast fiber end-face cleaning system provides a fast, effective, and cost-efficient solution for removing dirt and debris from connectors in most common applications. It is available in a benchtop and portable version
	FiberChek probe microscope	One-button FiberChek Probe delivers a reliable, fully autonomous, handheld inspection solution for every fiber technician.
	P5000i fiber microscope	Automated Fiber Inspection and Analysis Probe provides PASS/FAIL capability to PC, laptops, mobile devices and VIAVI test solutions.
Replacement Parts	Mating sleeves	AC500; FC/PC-FC/PC Universal Connector Adapter
		AC501; FC/PC-SC/PC Universal Connector Adapter
		AC502; FC/APC-FC/APC Universal Connector Adapter
		AC503; FC/APC-SC/APC Universal Connector Adapter

A wider range of inspection tools are available at VIAVI. More information about the products and accessories can be accessed through our website at www.viavisolutions.com. For further assistance please contact your local VIAVI account manager or VIAVI directly at 1-844-GO-VIAVI (1-844-468-4284) or to reach the VIAVI office nearest you, visit viavisolutions.com/contacts.

VIAVI Care Support Plans

Increase your productivity! Add a VIAVI Care Support Plan with your purchase for up to 5 years:

- Maintain your equipment for peak performance at a low, predictable cost
- Ensure accurate and repeatable measurements through VIAVI calibration
- Support Plans offer customers priority service and scheduling advantages to accelerate service
- Silver care always includes return-to-VIAVI calibration, but you can upgrade your support plan to include onsite calibration where available

Contact your local representative for more information on VIAVI Care Support Plan options or visit: viavisolutions.com/viavicareplan

Features

Plan	Objective	Technical Assistance	Factory Repair	Priority Service	Calibration
Manufacturer Warranty	Repair Manufacturer Defects	Standard Plus	✓		
 BronzeCare	Technician Efficiency	Premium	✓	✓	
 SilverCare	Maintenance and Measurement Accuracy	Premium	✓	✓	✓



Contact Us **+1 844 GO VIAVI**
(+1 844 468 4284)

To reach the VIAVI office nearest you,
visit viavisolutions.com/contact

© 2021 VIAVI Solutions Inc.
Product specifications and descriptions in this document are subject to change without notice.
Patented as described at
viavisolutions.com/patents
mtlgc2-ds-lab-nse-ae
30190909 902 1021

viavisolutions.com