Data Sheet



VIAVI

Nano and Micro iOTDR Cards

Medium and Long Range Integrated OTDR Fiber Testing Solutions

Gain a competitive advantage with the compact, easy to integrate VIAVI iOTDR™ cards and software. VIAVI iOTDR cards provide NEMS with the capability to help customers accurately locate fiber faults that degrade network traffic. Ensure high availability network services by identifying physical faults causing latency, jitter service quality issues and network outages. Protect data by detecting fiber security intrusion attacks.


VIAVI has specialized in OTDR design and production for over 30 years. VIAVI OTDRs offer unparalleled accuracy, ease of use and reliability that has been proven in rugged, portable instruments, rack mounted remote fiber test equipment and network elements. Select from our range of OTDR wavelengths, dynamic ranges and performance qualities to offer your customer the optimal solution for their inservice test applications.

Delivery of accurate, economical, low power, and easy to use OTDR technology requires years of experience, including an extensive software expertise in OTDR algorithms and user interface simplification to formulate an iOTDR card that is easy to implement for the non-OTDR expert.

- Accelerate your iOTDR integration design process by leveraging VIAVI professional services expertise to assist while you integrate and test the Nano or Micro iOTDR cards within a larger system.
- Provide an exceptionally accurate, reliable, low power, low cost, integrated OTDR. Offer in-service test and monitoring routines to characterize fiber, identify faults, detect intrusion attacks and track fiber degradation for preventative maintenance.



Nano iOTDR card



Micro IOTDR card

Features

- Medium or long distance OTDRs
- Short dead zone
- In-service fiber testing
- Controlled via Ethernet interface
- Large software library
- High distance accuracy
- Support from VIAVI OTDR experts for your development team
- For use in PON, XGS-PON, 5G. DWDM, CWDM and dark fiber testing

Applications

- Fiber characterization
- Fiber monitoring
- Tapping security intrusion detection
- Fault demarcation
- Raman amplified link test



Specifications Nano iOTDR card for Medium Range integrated OTDR – (typical at 25°C)



General		
Dimensions	98.5 x 67.5 x 16.5 mm	
Operating case temperature	-5 to 75°C	
Storage temperature	-40 to 85°C	
Humidity	5 to 85% without condensing	
EMC	EN61326-1, EN6100-3-2	
Interfaces	Ethernet 10/100	
Power consumption	5.1 W (Typical at 25°C) 10mW in standby mode	
OTDR		
Laser Safety	Class 1	
Number of data points	Up to 512,000	
Sampling resolution	From 4 cm	
Distance range	Up to 160 Km	
Distance accuracy	+/-1m +/- Sampling resolution +/- distance * 10-5	
OTDR Range Details	Medium Range	
Wavelength¹ (nm)	1610 nm	
Wavelength accuracy¹ (nm)	+/-5	
Dynamic range ² (dB)	32	
Pulse width	10 ns to 10 μs	
Event dead zone³ (m)	1.5	
Attenuation dead zone ⁴ (m)	5	

 $^{^{1}}$ Laser at 25 $^{\circ}$ C and measured at 10 μ s.

²The one way difference between the extrapolated backscattering level at the start of the fiber and the RMS noise level, after 3 minutes averaging and using the largest pulse width.

 $^{^3\}mbox{Measured}$ at ± 1.5 dB down from the peak of an unsaturated reflective event using the shortest pulse width.

 $^{^4\}mbox{Measured}$ at ± 0.5 dB from the linear regression using a -55dB type reflectance and using the shortest pulse width.

Specifications Micro iOTDR card for Medium or Long Range integrated OTDR – (typical at 25°C)



General			
Dimensions	91 x 170 x 16.5 mm		
Operating temperature	-5 to 65°C or 70°C according to the variant		
Storage temperature	-20 to 85°C		
Humidity	85% without condensing		
EMC	EN61326-1, EN6100-3-2		
Interfaces	Ethernet 10/100/1000		
Power consumption	5.1 W (Typical at 25°C) 10mW in standby mode		
OTDR			
Laser Safety	Class 1		
Number of data points	Up to 512,000		
Sampling resolution	From 4 cm		
Distance range	Up to 260 Km		
Distance accuracy	+/-1m +/- Sampling resolution +/- distance * 10-5		
OTDR Range Details	Medium Range	Long Range	
Wavelength¹ (nm)	1625 nm	1610 or 1626 nm	
Wavelength accuracy¹ (nm)	+/-3	+/-3	
Dynamic range² (dB)	37	40	
Pulse width	5 ns to 20 μs	5ns to 20 μs	
Event dead zone³ (m)	1	0.8	
Attenuation dead zone⁴ (m)	3.5	3	

 $^{^{1}}Laser$ at 25°C and measured at 10 $\mu s.$



Contact Us

+1 844 GO VIAVI (+1 844 468 4284)

To reach the VIAVI office nearest you, visit viavisolutions.com/contact

© 2022 VIAVI Solutions Inc. Product specifications and descriptions in this document are subject to change without notice. nanomicro-iotdrcard-ds-fop-nse-ae 30192951 902 0722

²The one way difference between the extrapolated backscattering level at the start of the fiber and the RMS noise level, after 3 minutes averaging and using the largest pulse width.

 $^{^3}$ Measured at ± 1.5 dB down from the peak of an unsaturated reflective event using the shortest pulse width.

 $^{^4}$ Measured at ± 0.5 dB from the linear regression using a -55dB type reflectance and using the shortest pulse width.